

Coaxial Cable Connector 16_C-50-7-6/133_N

Description

Right angle cable plug

Interface standards

IEC 60169-7_MIL-STD-348A/302

Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	11 GHz

Mechanical Data

Centre contact	soldered
Outer contact	clamped
Weight	0.0761 kg

Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium / Brass	SUCOPRO / Gold Plating
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	

Related Documents

Outline drawing	DOU-00008274
Catalogue drawing	DCA-00198839
Assembly instruction	DOC-0000184392

Ordering Information

Single package	16_C-50-7-6/133_NE
----------------	--------------------

Additional Information

Suitable cables	RG_214_/U, GX_07272, RG_213_/U
-----------------	--------------------------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HUBER+SUHNER:

16_C-50-7-6/133_NE