

Coaxial Cable Connector 16_N-50-12-61/033_-

Description

Right angle cable plug

Interface standards

IEC 61169-4_CECC 22190_DIN 47223_VG 95250



Technical Data

Electrical Data

Impedance	50 Ω	
Interface frequency max.	11 GHz	
Frequency range	DC to 2.7 GHz	2.7 to 3.7 GHz
Return loss	30 dB	28 dB

Mechanical Data

Centre contact	plugged
Outer contact	clamped
Weight	0.13 kg

Environmental Data

Operating temperature	-40 °C to 85 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	Silver Plating
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	NR (Natural Rubber)	

Related Documents

Outline drawing	DOU-00326031
Catalogue drawing	DCA-00345494
Assembly instruction	DOC-0000799919

Ordering Information

Single package	16_N-50-12-61/033_-E
----------------	----------------------

Additional Information

Remarks

Other suitable cable: ANDREW/COMMScope LDF4-50A / Assembly instructions: Foam-DOC-0000799919, Plenum-DOC-0000736630 / Note: Use blade unit 74_Z-0-12-20, 85069095 (colour yellow)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HUBER+SUHNER:

16_N-50-12-61/033_-E