

Coaxial Cable Connector 16_QMA-50-3-1/133_N

Description

Right angle cable plug

Interface standards

QMA QLF compliant



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	18 GHz

Mechanical Data

Centre contact	soldered
Outer contact	crimped
Weight	0.0081 kg

Environmental Data

Operating temperature	-40 °C to 85 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	SUCOPRO Plating
Outer contact	Bronze	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Crimp ferrule	Copper	SUCOPLATE (R) Plating

Related Documents

Outline drawing	DOU-00005830
Catalogue drawing	DOU-00005832
Assembly instruction	DOC-0000178735

Ordering Information

Bulk 100 pcs package	16_QMA-50-3-1/133_NH
Single package	16_QMA-50-3-1/133_NE

Additional Information

Suitable cables	RG_400_/U, RG_223_/U, ENVIROFLEX_400, RADOX_RF_400, ENVIROFLEX_142, RADOX_RF_142
-----------------	--

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HUBER+SUHNER:

16_QMA-50-3-1/133_NH