

Coaxial Cable Connector 16_QN-50-7-1/133_N

Description

Right angle cable plug

Interface standards
QN QLF compliant



Technical Data

Electrical Data

Impedance	50 Ω		
Interface frequency max.	11 GHz		
Frequency range	DC to 2 GHz	2 to 4 GHz	4 to 6 GHz
Return loss	30 dB	28 dB	24 dB

Mechanical Data

Centre contact	soldered
Outer contact	crimped
Weight	0.0366 kg

Environmental Data

Operating temperature	-40 °C to 125 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	SUCOPRO Plating
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	EPDM (Ethylene propylene diene rubber)	
Crimp ferrule	Copper	SUCOPLATE (R) Plating

Related Documents

Outline drawing	DOU-00006246
Catalogue drawing	DOU-00006248
Assembly instruction	DOC-0000179449

Ordering Information

Single package	16_QN-50-7-1/133_NE
----------------	---------------------

Additional Information

Suitable cables	ENVIROFLEX_393, RG_393_/U, RG_214_/U, GX_07272_D-04, RADOX_RF_214
-----------------	---

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HUBER+SUHNER:

[16_QN-50-7-1/133_NE](#)