

## Coaxial Cable Connector 16\_SMB-50-2-40/111\_N

### Description

Right angle cable plug

Interface standards

IEC 60169-10\_MIL-STD-348A/311\_CECC 22130



### Technical Data

#### Electrical Data

|                          |             |
|--------------------------|-------------|
| Impedance                | 50 $\Omega$ |
| Interface frequency max. | 4 GHz       |

#### Mechanical Data

|                |           |
|----------------|-----------|
| Centre contact | crimped   |
| Outer contact  | crimped   |
| Weight         | 0.0042 kg |

#### Environmental Data

|                                                      |                  |
|------------------------------------------------------|------------------|
| Operating temperature                                | -65 °C to 165 °C |
| 2011/65/EU (RoHS - including 2015/863 and 2017/2102) | compliant        |

#### Material Data

| Piece Parts    | Material               | Surface Plating                            |
|----------------|------------------------|--------------------------------------------|
| Centre contact | Copper Beryllium Alloy | Gold Plating (Nickel underplated)          |
| Outer contact  | Brass                  | Gold Plating (Nickel underplated)          |
| Body           | Brass                  | Gold Plating (Nickel underplated)          |
| Insulator      | PFA / PTFE             |                                            |
| Crimp ferrule  | Copper                 | Gold Plating (without Nickel underplating) |

### Related Documents

|                      |                |
|----------------------|----------------|
| Outline drawing      | DOU-00007164   |
| Catalogue drawing    | DOU-00006816   |
| Assembly instruction | DOC-0000179157 |

### Ordering Information

|                      |                       |
|----------------------|-----------------------|
| Single package       | 16_SMB-50-2-40/111_NE |
| Bulk 100 pcs package | 16_SMB-50-2-40/111_NH |

### Additional Information

|                 |                                                  |
|-----------------|--------------------------------------------------|
| Suitable cables | RG_316_/U, ENVIROFLEX_316, RG_188_A/U, RG_174_/U |
|-----------------|--------------------------------------------------|

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HUBER+SUHNER:

[16\\_SMB-50-2-40/111\\_NE](#)