

Coaxial Cable Connector 21_4310-50-3-1/003_-

Description

Straight cable jack

Interface standards
IEC 61169-54



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	12 GHz

Mechanical Data

Centre contact	soldered
Outer contact	soldered

Environmental Data

Operating temperature	-55 °C to 90 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium / Brass	Silver Plating
Outer contact	Bronze	Silver Plating
Body	Brass	SUCOPLATE (R) Plating
Other body part	Brass	Silver Plating
Insulator	PTFE (Polytetrafluoroethylene)	

Related Documents

Outline drawing	DOU-00300201
Catalogue drawing	DCA-00327124
Assembly instruction	DOC-0000717634

Ordering Information

Tray package	21_4310-50-3-1/003_-Y
--------------	-----------------------

Additional Information

Suitable cables	SUCOFORM_141, EZ_141_AL_TP_M17, MULTIFLEX_141
-----------------	---

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HUBER+SUHNER:

21_4310-50-3-1/003_-Y