

Coaxial Cable Connector 21_BNC-50-2-16/133_N

Description

Straight cable jack

Interface standards

IEC 60169-8_MIL-STD-348A/301_CECC 22120

Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	4 GHz

Mechanical Data

Centre contact	crimped
Outer contact	crimped
Weight	0.0131 kg

Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium / Brass	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Crimp ferrule	Copper	SUCOPLATE (R) Plating

Related Documents

Outline drawing	DOU-00008218
Assembly instruction	DOC-0000179123

Ordering Information

Single package	21_BNC-50-2-16/133_NE
----------------	-----------------------

Additional Information

Suitable cables	G_01130_HT
-----------------	------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HUBER+SUHNER:](#)

[21_BNC-50-2-16/133_NE](#)