

Coaxial Cable Connector 21_C-50-7-3/122_N

Description

Straight cable jack

Interface standards

IEC 60169-7_MIL-STD-348A/302

Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	11 GHz

Mechanical Data

Centre contact	soldered
Outer contact	clamped
Weight	0.0365 kg

Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	Nickel Plating
Body	Brass	Nickel Plating
Insulator	PFA / PTFE	
Gasket	VMQ (Silicone rubber)	

Related Documents

Outline drawing	DOU-00162670
Catalogue drawing	DCA-00005915
Assembly instruction	DOC-0000179115

Ordering Information

Single package	21_C-50-7-3/122_NE
----------------	--------------------

Additional Information

Suitable cables	RG_214_/U, RG_393_/U, GX_07272_D
-----------------	----------------------------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HUBER+SUHNER:

21_C-50-7-3/122_NE