

Coaxial Cable Connector 21_PC185-50-2-5/19-_NE

Description

Straight cable jack

Interface standards



Technical Data

Electrical Data

Impedance	50 Ω	
Interface frequency max.	67 GHz	
Frequency range	DC to 50 GHz	50 to 67 GHz
Return loss	24 dB	20 dB

Mechanical Data

Centre contact	plugged
Outer contact	soldered
Weight	0.004 kg

Environmental Data

Operating temperature	-55 °C to 155 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	SUCOPRO / Gold Plating
Outer contact	Stainless Steel	Passivated (Plating)
Body	Stainless Steel	Passivated (Plating)
Insulator	LCP (Liquid crystal polymer)	

Related Documents

Outline drawing	DOU-00235464
Catalogue drawing	DCA-00234990
Assembly instruction	DOC-0000397354

Ordering Information

Single package	21_PC185-50-2-5/19-_NE
----------------	------------------------

Additional Information

Suitable cables	SR_86_LA, SR_86_TP_LA
-----------------	-----------------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HUBER+SUHNER:

21_PC185-50-2-5/19-_NE