

Coaxial Cable Connector 21_SMPSL-50-3-1C

Description

Straight cable jack

Interface standards

MIL-STD-348, MIL-PRF-31031, DSCC 06026



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	40 GHz

Mechanical Data

Weight	0.00127 kg
--------	------------

Environmental Data

Operating temperature	-55 °C to 125 °C
-----------------------	------------------

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Body	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Insulator	PTFE (Polytetrafluoroethylene)	
Coupling nut	Stainless Steel	Gold Plating (Nickel underplated)

Ordering Information

Additional Information

Suitable cables	32022
-----------------	-------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HUBER+SUHNER:

[21_SMPSL-50-3-1C](#)