

Coaxial Cable Connector 21_UHF-0-3-3/033_

Description

Straight cable jack

Interface standards
IEC 60169-12



Technical Data

Electrical Data

Impedance	other Ω
Interface frequency max.	0.2 GHz

Mechanical Data

Centre contact	crimped
Outer contact	crimped
Weight	0.0301 kg

Environmental Data

Operating temperature	-55 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	Silver Plating
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Crimp ferrule	Copper	SUCOPLATE (R) Plating

Related Documents

Outline drawing	DOU-00181692
Catalogue drawing	DCA-00005871
Assembly instruction	DOC-0000201061

Ordering Information

Single package	21_UHF-0-3-3/033_-E
----------------	---------------------

Additional Information

Suitable cables	RG_58_C/U, G_03232, GX_03272
-----------------	------------------------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HUBER+SUHNER:

21_UHF-0-3-3/033_-E