

Coaxial Panel Connector 22_MMBX-50-0-2/111_N

Description

Straight bulkhead receptacle jack

Interface standards
SUHNER-MMBX



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	12.4 GHz

Mechanical Data

Number of matings	100
Weight	0.0011 kg

Environmental Data

Operating temperature	-55 °C to 155 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPRO Plating
Body	Brass	SUCOPRO Plating
Insulator	PTFE / LCP	

Related Documents

Outline drawing	DOU-00017333
Catalogue drawing	DCA-00086279
Mounting hole	DCA-00086278

Ordering Information

Tray package	22_MMBX-50-0-2/111_NY
--------------	-----------------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HUBER+SUHNER:

[22_MMBX-50-0-2/111_NY](#)