

Coaxial Panel Connector 22_QLA-01-0-2/112_N

Description

Straight bulkhead receptacle jack

Interface standards

NIM-CAMAC-Standard CD/N549



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	1.4 GHz

Mechanical Data

Number of matings	10000
Weight	0.0031 kg

Environmental Data

Operating temperature	-55 °C to 150 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Bronze	Gold Plating (Nickel underplated)
Body	Brass	Nickel Plating
Insulator	PFA / PTFE	
Fastening nut	Brass	Nickel Plating
Washer	Brass	Nickel Plating

Related Documents

Catalogue drawing	DCA-00010451
Mounting hole	DOU-00009113

Ordering Information

Single package	22_QLA-01-0-2/112_NE
----------------	----------------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HUBER+SUHNER:

[22_QLA-01-0-2/112_NE](#)