

## Coaxial Panel Connector 22\_SHV-50-0-6/133\_N

### Description

Straight bulkhead receptacle jack

Interface standards  
IEC 60498\_MIL-STD-348A/314



### Technical Data

#### Electrical Data

Impedance 50  $\Omega$   
Interface frequency max. 0.3 GHz

#### Mechanical Data

Chassis torque 2 Nm  
Number of matings 500  
Weight 0.0111 kg

#### Environmental Data

Operating temperature -55 °C to 100 °C  
2011/65/EU (RoHS - including  
2015/863 and 2017/2102) compliant

#### Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PS (Polystyrene)	
Fastening nut	Brass	SUCOPLATE (R) Plating
Washer	Bronze	SUCOPLATE (R) Plating

### Related Documents

Outline drawing DOU-00011058  
Catalogue drawing DCA-00010449  
Mounting hole DOU-00008762

### Ordering Information

Single package 22\_SHV-50-0-6/133\_NE

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HUBER+SUHNER:

[22\\_SHV-50-0-6/133\\_NE](#)