

Coaxial Panel Connector 22_SMC-50-0-3/111_N

Description

Straight bulkhead receptacle jack

Interface standards

IEC 60169-9_MIL-STD-348A/312_CECC 22140



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	10 GHz

Mechanical Data

Number of matings	500
Weight	0.0011 kg

Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer contact	Brass	Gold Plating (Nickel underplated)
Body	Brass	Gold Plating (Nickel underplated)
Insulator	PFA / PTFE	
Fastening nut	Brass	Gold Plating (Nickel underplated)
Washer	Bronze	Gold Plating (Nickel underplated)

Related Documents

Catalogue drawing	DCA-00011570
Mounting hole	DOU-00008855

Ordering Information

Single package	22_SMC-50-0-3/111_NE
----------------	----------------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HUBER+SUHNER:

[22_SMC-50-0-3/111_NE](#)