

Coaxial Panel Connector 23_NEX10-50-0-3/033_-

Description

Straight panel receptacle jack, flange mount

Interface standards
NEX10



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	20 GHz

Environmental Data

Operating temperature 2011/65/EU (RoHS - including 2015/863 and 2017/2102)	-55 °C to 125 °C compliant
--	-------------------------------

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Silver Plating
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	

Related Documents

Outline drawing	DOU-00344002
-----------------	--------------

Ordering Information

Tray package	23_NEX10-50-0-3/033_-Y
--------------	------------------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HUBER+SUHNER:

23_NEX10-50-0-3/033_-Y