

Coaxial Panel Connector
23_QMA-50-0-2/111_N

Description

Straight panel receptacle plug, flange mount

Interface standards
QMA QLF compliant



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	6 GHz

Mechanical Data

Number of matings	100
Weight	0.0023 kg

Environmental Data

Operating temperature	-40 °C to 80 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	SUCOPRO Plating
Outer contact	Brass	SUCOPRO Plating
Body	Brass	SUCOPRO Plating
Insulator	PFA / PTFE	

Related Documents

Outline drawing	DOU-00011474
Catalogue drawing	DCA-00011476

Ordering Information

Bulk 100 pcs package	23_QMA-50-0-2/111_NH
----------------------	----------------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HUBER+SUHNER:

23_QMA-50-0-2/111_NH