

## Coaxial Panel Connector 23\_SMA-50-0-51/199\_N

### Description

Straight panel receptacle jack, flange mount

Interface standards

IEC 60169-15\_MIL-STD-348A/310\_CECC 22110



### Technical Data

#### Electrical Data

Impedance	50 $\Omega$
Interface frequency max.	18 GHz

#### Mechanical Data

Number of matings	500
Weight	0.0025 kg

#### Environmental Data

Operating temperature	-65 °C to 125 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

#### Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Stainless Steel	
Body	Stainless Steel	
Insulator	PFA / PTFE	

### Related Documents

Outline drawing	DOU-00011515
Catalogue drawing	DCA-00010331

### Ordering Information

Single package	23_SMA-50-0-51/199_NE
----------------	-----------------------

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HUBER+SUHNER:

[23\\_SMA-50-0-51/199\\_NE](#)