

Coaxial Panel Connector 23_TNC-50-0-6/133_N

Description

Straight panel receptacle jack, flange mount

Interface standards

IEC 60169-17_MIL-STD-348A/313_CECC 22200



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	11 GHz

Mechanical Data

Number of matings	500
Weight	0.0174 kg

Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	

Related Documents

Outline drawing	DOU-00010054
Catalogue drawing	DCA-00010056
Mounting hole	DOU-00010057

Ordering Information

Single package	23_TNC-50-0-6/133_NE
----------------	----------------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HUBER+SUHNER:

[23_TNC-50-0-6/133_NE](#)