

Coaxial Cable Connector 24_BNO-0-4-1/133_N

Description

Straight bulkhead cable feed through

Interface standards
IEC 60169-22



Technical Data

Electrical Data

Impedance	not defined Ω
Interface frequency max.	0.2 GHz

Mechanical Data

Centre contact	soldered
Outer contact	crimped
Weight	0.0202 kg

Environmental Data

Operating temperature	-50 °C to 125 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium / Brass	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	ETFE (Ethylene tetrafluoroethylene)	
Gasket	VMQ (Silicone rubber)	
Fastening nut	Brass	SUCOPLATE (R) Plating
Washer	Bronze	SUCOPLATE (R) Plating
Crimp ferrule	Copper	SUCOPLATE (R) Plating

Related Documents

Outline drawing	DOU-00008925
Catalogue drawing	DCA-00008927
Assembly instruction	DOC-0000180938
Mounting hole	DOU-00008751

Ordering Information

Single package	24_BNO-0-4-1/133_NE
----------------	---------------------

Additional Information

Suitable cables	RG_108_A/U, K_05790
-----------------	---------------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HUBER+SUHNER:

[24_BNO-0-4-1/133_NE](#)