

Coaxial Cable Connector 24_C-50-3-2/133_N

Description

Straight bulkhead cable feed through

Interface standards

IEC 60169-7_MIL-STD-348A/302

Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	11 GHz

Mechanical Data

Centre contact	soldered
Outer contact	clamped
Weight	0.0424 kg

Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	SUCOPRO / Gold Plating
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Gasket	VMQ (Silicone rubber)	
Fastening nut	Brass	SUCOPLATE (R) Plating
Washer	Bronze	SUCOPLATE (R) Plating

Related Documents

Outline drawing	DOU-00009842
Catalogue drawing	DCA-00009844
Assembly instruction	DOC-0000177464
Mounting hole	DOU-00009577

Ordering Information

Single package	24_C-50-3-2/133_NE
----------------	--------------------

Additional Information

Suitable cables	RG_223_/U, RG_142_B/U
-----------------	-----------------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HUBER+SUHNER:

24_C-50-3-2/133_NE