

Coaxial Cable Connector 24_N-50-3-45/133_N

Description

Straight bulkhead cable jack

Interface standards

IEC 61169-16_MIL-STD-348A/304_CECC 22210

Technical Data

Electrical Data

Impedance	50 Ω		
Interface frequency max.	11 GHz		
Frequency range	DC to 2 GHz	2 to 4 GHz	4 to 6 GHz
Return loss	31 dB	30.2 dB	24 dB

Mechanical Data

Centre contact	plugged
Outer contact	crimped
Weight	0.041547 kg

Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	SUCOPRO Plating
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PTFE (Polytetrafluoroethylene)	
Fastening nut	Brass	SUCOPLATE (R) Plating
Washer	Bronze	SUCOPLATE (R) Plating
Crimp ferrule	Copper	SUCOPLATE (R) Plating

Related Documents

Outline drawing	DOU-00303913
Assembly instruction	DOC-0000721787
Mounting hole	DPA-00001434

Ordering Information

Bulk 100 pcs package	24_N-50-3-45/133_NH
Single package	24_N-50-3-45/133_NE

Additional Information

Suitable cables	SPUMA_195
-----------------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HUBER+SUHNER:

[24_N-50-3-45/133_NH](#)