

Coaxial Cable Connector 24_QMA-50-2-1/111_N

Description

Straight bulkhead cable feed through

Interface standards
QMA QLF compliant



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	18 GHz

Mechanical Data

Centre contact	plugged
Outer contact	soldered
Weight	0.0041 kg

Environmental Data

Operating temperature	-40 °C to 85 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	SUCOPRO Plating
Outer contact	Brass	SUCOPRO Plating
Body	Brass	SUCOPRO Plating
Insulator	PFA / PTFE	
Gasket	VMQ (Silicone rubber)	
Fastening nut	Brass	SUCOPRO Plating
Washer	Bronze	SUCOPRO Plating

Related Documents

Outline drawing	DOU-00009765
Catalogue drawing	DCA-00009767
Assembly instruction	DOC-0000389604
Mounting hole	DOU-00008748

Ordering Information

Single package	24_QMA-50-2-1/111_NE
Bulk 100 pcs package	24_QMA-50-2-1/111_NH

Additional Information

Suitable cables	SUCOFORM_86, EZ_86_TP_M17, MULTIFLEX_86
-----------------	---

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HUBER+SUHNER:

24_QMA-50-2-1/111_NH