

Coaxial Cable Connector 24_SMA-50-3-17/111_N

Description

Straight bulkhead cable feed through

Interface standards

IEC 60169-15_MIL-STD-348A/310_CECC 22110

Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	18 GHz

Mechanical Data

Centre contact	soldered
Outer contact	soldered
Weight	0.0033 kg

Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	SUCOPRO Plating
Outer contact	Brass	SUCOPRO Plating
Body	Brass	SUCOPRO Plating
Insulator	PFA / PTFE	
Gasket	VMQ (Silicone rubber)	
Fastening nut	Brass	SUCOPRO Plating
Washer	Bronze	SUCOPRO Plating

Related Documents

Outline drawing	DOU-00047486
Catalogue drawing	DCA-00177001
Assembly instruction	DOC-0000181605

Ordering Information

Bulk 100 pcs package	24_SMA-50-3-17/111_NH
----------------------	-----------------------

Additional Information

Suitable cables	SUCOFORM_141, EZ_141_M17, MULTIFLEX_141
-----------------	---

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HUBER+SUHNER:

[24_SMA-50-3-17/111_NH](#)