

## Coaxial Cable Connector 24\_SMA-50-3-42/133\_N

### Description

Straight bulkhead cable feed through

Interface standards

IEC 60169-15\_MIL-STD-348A/310\_CECC 22110



### Technical Data

#### Electrical Data

|                          |        |
|--------------------------|--------|
| Impedance                | 50 Ω   |
| Interface frequency max. | 18 GHz |

#### Mechanical Data

|                |           |
|----------------|-----------|
| Centre contact | soldered  |
| Outer contact  | crimped   |
| Weight         | 0.0044 kg |

#### Environmental Data

|                                                      |                  |
|------------------------------------------------------|------------------|
| Operating temperature                                | -65 °C to 165 °C |
| 2011/65/EU (RoHS - including 2015/863 and 2017/2102) | compliant        |

#### Material Data

| Piece Parts    | Material               | Surface Plating                   |
|----------------|------------------------|-----------------------------------|
| Centre contact | Copper Beryllium Alloy | Gold Plating (Nickel underplated) |
| Outer contact  | Brass                  | SUCOPLATE (R) Plating             |
| Body           | Brass                  | SUCOPLATE (R) Plating             |
| Insulator      | PFA / PTFE             |                                   |
| Fastening nut  | Brass                  | SUCOPLATE (R) Plating             |
| Washer         | Bronze                 | SUCOPLATE (R) Plating             |
| Crimp ferrule  | Copper                 | SUCOPLATE (R) Plating             |

### Related Documents

|                      |                |
|----------------------|----------------|
| Outline drawing      | DOU-00009258   |
| Catalogue drawing    | DCA-00009259   |
| Assembly instruction | DOC-0000184970 |
| Mounting hole        | DOU-00008748   |

### Ordering Information

|                |                       |
|----------------|-----------------------|
| Single package | 24_SMA-50-3-42/133_NE |
|----------------|-----------------------|

### Additional Information

|                 |                                       |
|-----------------|---------------------------------------|
| Suitable cables | RG_223_/U, ENVIROFLEX_142, RG_142_B/U |
|-----------------|---------------------------------------|

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HUBER+SUHNER:

[24\\_SMA-50-3-42/133\\_NE](#)