


Coaxial Panel Connector 28_SMA-50-0-1/111_N

Description

Right angle panel receptacle jack, flange mount

Interface standards

IEC 60169-15_MIL-STD-348A/310_CECC 22110



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	18 GHz

Mechanical Data

Number of matings	500
Weight	0.0057 kg

Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium / Brass	Gold Plating (Nickel underplated)
Outer contact	Copper Beryllium / Brass	Gold Plating (Nickel underplated)
Body	Copper Beryllium / Brass	Gold Plating (Nickel underplated)
Insulator	PFA / PTFE	

Related Documents

Outline drawing	DOU-00108650
Catalogue drawing	DCA-00010294

Ordering Information

Single package	28_SMA-50-0-1/111_NE
----------------	----------------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HUBER+SUHNER:

[28_SMA-50-0-1/111_NE](#)