

Within Series Adaptor 31_N-75-0-2/133_N

Description

Adaptor jack/jack
N jack (female) / N jack (female)

Interface standard
Series N - Not compatible to N 50 Ohms



Technical Data

Electrical Data

Impedance	75 Ω
Interface frequency max.	1.5 GHz

Mechanical Data

Number of matings	500
Weight	0.0386 kg

Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Interface - N jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	

Interface - N jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	

Related Documents

Catalogue drawing	DCA-00013814
-------------------	--------------

Ordering Information

Single package	31_N-75-0-2/133_NE
----------------	--------------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HUBER+SUHNER:

[31_N-75-0-2/133_NE](#)