

Within Series Adaptor 31_QLA-01-0-1/112_N

Description

Adaptor jack/jack
QLA-01 jack (female) / QLA-01 jack (female)

Interface standard
Series QLA-01 - NIM-CAMAC-Standard CD/N549



Technical Data

Electrical Data

Impedance	other Ω
Interface frequency max.	1.4 GHz

Mechanical Data

Number of matings	10000
Weight	0.0042 kg

Environmental Data

Operating temperature	-55 °C to 150 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Interface - QLA-01 jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Bronze	Gold Plating (Nickel underplated)
Body	Brass	Nickel Plating
Insulator	PFA / PTFE	

Interface - QLA-01 jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Bronze	Gold Plating (Nickel underplated)
Body	Brass	Nickel Plating
Insulator	PFA / PTFE	

Related Documents

Catalogue drawing	DCA-00013895
-------------------	--------------

Ordering Information

Single package	31_QLA-01-0-1/112_NE
----------------	----------------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HUBER+SUHNER:

[31_QLA-01-0-1/112_NE](#)