

## Between Series Adaptor 33\_N-MCX-50-1/1--\_U

### Description

Adaptor plug/jack  
N plug (male) / MCX jack (female)

Interface standards  
Series N - IEC 61169-16\_MIL-STD-348A/304\_CECC 22210  
Series MCX - IEC 60169-36\_CECC 22220



### Technical Data

#### Electrical Data

|                          |                                     |
|--------------------------|-------------------------------------|
| Impedance                | 50 Ω                                |
| Interface frequency max. | 6 GHz                               |
| VSWR                     | DC - 6 GHz<br>≤ 1.03 + 0.03 f (GHz) |

#### Mechanical Data

|                   |           |
|-------------------|-----------|
| Number of matings | 500       |
| Weight            | 0.0293 kg |

#### Environmental Data

|                                                      |                  |
|------------------------------------------------------|------------------|
| Operating temperature                                | -55 °C to 155 °C |
| 2011/65/EU (RoHS - including 2015/863 and 2017/2102) | compliant        |

#### Material Data

Interface - N plug (male)

| Piece Parts    | Material               | Surface Plating                            |
|----------------|------------------------|--------------------------------------------|
| Centre contact | Copper Beryllium Alloy | Gold Plating (without Nickel underplating) |
| Outer contact  | Brass                  | SUCOPLATE (R) Plating                      |
| Body           | Brass                  | SUCOPLATE (R) Plating                      |
| Insulator      | PFA / PTFE             |                                            |
| Coupling nut   | Brass                  | SUCOPLATE (R) Plating                      |
| Gasket         | VMQ (Silicone rubber)  |                                            |

Interface - MCX jack (female)

| Piece Parts    | Material               | Surface Plating                            |
|----------------|------------------------|--------------------------------------------|
| Centre contact | Copper Beryllium Alloy | Gold Plating (without Nickel underplating) |
| Outer contact  | Brass                  | Gold Plating (without Nickel underplating) |
| Body           | Brass                  | SUCOPLATE (R) Plating                      |
| Insulator      | PFA / PTFE             |                                            |

### Related Documents

|                   |              |
|-------------------|--------------|
| Catalogue drawing | DCA-00014319 |
|-------------------|--------------|

### Ordering Information

|                |                      |
|----------------|----------------------|
| Single package | 33_N-MCX-50-1/1--_UE |
|----------------|----------------------|

## Between Series Adaptor 33\_N-MCX-50-1/1--\_U

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HUBER+SUHNER:

[33\\_N-MCX-50-1/1--\\_UE](#)