

Between Series Adaptor 33_PC35-NEX10-50-1/199_N

Description

Adaptor plug/jack
PC 3.5 plug (male) / NEX10 jack (female)

Interface standards
Series PC 3.5 - IEC 60169-23
Series NEX10 - Standard



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	20 GHz

Environmental Data

Operating temperature	-55 °C to 100 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Interface - PC 3.5 plug (male)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	SUCOPRO Plating
Outer contact	Stainless Steel	
Body	Stainless Steel	
Insulator		
Coupling nut	Stainless Steel	

Interface - NEX10 jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	SUCOPRO Plating
Outer contact	Stainless Steel	
Body	Stainless Steel	
Insulator	PTFE (Polytetrafluoroethylene)	

Related Documents

Catalogue drawing	DCA-00343963
-------------------	--------------

Ordering Information

Single package	33_PC35-NEX10-50-1/199_NE
----------------	---------------------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HUBER+SUHNER:

[33_PC35-NEX10-50-1/199_NE](#)