

## Within Series Adaptor 46\_BNC-75-0-1/133\_N

### Description

T-adaptor, 3 jacks  
BNC jack (female) / BNC jack (female)

Interface standard  
Series BNC - Compatible with IEC 61169-8\_MIL-STD-348A/301\_CECC 22120



### Technical Data

#### Electrical Data

Impedance 75 Ω  
Interface frequency max. 1 GHz

#### Mechanical Data

Number of matings 500  
Weight 0.0118 kg

#### Environmental Data

Operating temperature -65 °C to 165 °C  
2011/65/EU (RoHS - including  
2015/863 and 2017/2102) compliant

#### Material Data

Interface - BNC jack (female)

| Piece Parts    | Material               | Surface Plating                   |
|----------------|------------------------|-----------------------------------|
| Centre contact | Copper Beryllium Alloy | Gold Plating (Nickel underplated) |
| Outer contact  | Brass                  | SUCOPLATE (R) Plating             |
| Body           | Brass                  | SUCOPLATE (R) Plating             |
| Insulator      | PFA / PTFE             |                                   |

Interface - BNC jack (female)

| Piece Parts    | Material               | Surface Plating                   |
|----------------|------------------------|-----------------------------------|
| Centre contact | Copper Beryllium Alloy | Gold Plating (Nickel underplated) |
| Outer contact  | Brass                  | SUCOPLATE (R) Plating             |
| Body           | Brass                  | SUCOPLATE (R) Plating             |
| Insulator      | PFA / PTFE             |                                   |

### Related Documents

Catalogue drawing DCA-00013495

### Ordering Information

Single package 46\_BNC-75-0-1/133\_NE

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HUBER+SUHNER:

[46\\_BNC-75-0-1/133\\_NE](#)