

RF TERMINATION Type 6506.26.0002

Description

Standard Termination, Medium Power



Product Configuration

Connector	TNC plug (male)
Interface standards	IEC 60169-17_MIL-STD-348A/313_CECC 22200

Technical Data

Electrical Data

Nominal Impedance	50 Ω		
Frequency range	0 to 6 GHz		
Frequency sub range	DC to 2 GHz	2 to 4 GHz	4 to 6 GHz
VSWR max.	1.1	1.2	1.25
Power rating	6 Watt average power up to 40 °C ambient temperature, linearly derated to 0 Watt at 130 °C ambient temperature. 1000 Watt peak power , 5 μ s pulse, 0.05 % duty cycle		

Mechanical Data

Weight	0.062 kg
--------	----------

Environmental Data

Operating temperature	-40 °C to 130 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	not compliant

Material Data

Piece Part	Material	Surface Plating
Centre contact	Bronze	Gold Plating (without Nickel underplating)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Aluminium	
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating

Related Documents

Outline drawing	DOU-00005433
-----------------	--------------

Ordering Information

Single Packaging	6506.26.0002
Packaging	

Additional Information

Important note	WARNING Beryllia Ceramic Inside! DO NOT sand, scrap or tamper with. Dispose in accordance with all relevant regulations.
----------------	--

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HUBER+SUHNER:](#)

[6506.26.0002](#)