


Coaxial PCB Connector 82_MCX-S75-0-2/111_N

Description

Straight PCB jack

Interface Standards
IEC 60169-36_CECC 22220



Technical Data

Electrical Data

Impedance 75 Ω
Interface frequency max. 6 GHz

Mechanical Data

Board mounting type edge mount
Weight 0.0009 kg

Environmental Data

Operating temperature -65 °C to 165 °C
2011/65/EU (RoHS - including
2015/863 and 2017/2102) compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	SUCOPRO Plating
Outer contact	Brass	SUCOPRO Plating
Body	Brass	SUCOPRO Plating
Insulator	PFA / PTFE	

Related Documents

Outline drawing DOU-00013375
Catalogue drawing DCA-00013377

Ordering Information

Single package 82_MCX-S75-0-2/111_NE
Bulk 100 pcs package 82_MCX-S75-0-2/111_NH

Remarks

PCB connector without stand-offs

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HUBER+SUHNER:](#)

[82_MCX-S75-0-2/111_NH](#)