

Coaxial PCB Connector 82_MFBX-50-0-3/111_N

Description

Straight PCB jack

Interface Standards
HUBER+SUHNER MFBX



Technical Data

Electrical Data

Impedance 50 Ω
Interface frequency max. 6 GHz

Mechanical Data

Board mounting type through holes
Weight 0.000602 kg

Environmental Data

Operating temperature -55 °C to 155 °C
2011/65/EU (RoHS - including
2015/863 and 2017/2102) compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	SUCOPRO Plating
Outer contact	Brass	SUCOPRO Plating
Body		
Insulator	LCP (Liquid crystal polymer)	

Related Documents

Outline drawing DOU-00246021
Catalogue drawing DCA-00275261

Ordering Information

Single package 82_MFBX-50-0-3/111_NE

Remarks

PCB connector with stand-offs

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HUBER+SUHNER:

[82_MFBX-50-0-3/111_NE](#)