

Coaxial PCB Connector
82_MFBX-50-0-4/111_N

Description

Straight PCB jack

Interface Standards
HUBER+SUHNER MFBX



Technical Data

Electrical Data

Impedance 50 Ω
Interface frequency max. 6 GHz

Mechanical Data

Board mounting type through holes
Weight 0.003255 kg

Environmental Data

Operating temperature -55 °C to 155 °C
2011/65/EU (RoHS - including
2015/863 and 2017/2102) compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	SUCOPRO Plating
Outer contact	Brass	SUCOPRO Plating
Body	PA (Polyamide)	
Insulator	LCP (Liquid crystal polymer)	

Related Documents

Outline drawing DOU-00246036
Catalogue drawing DCA-00275274

Ordering Information

Single package 82_MFBX-50-0-4/111_NE

Remarks

PCB connector with stand-offs

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HUBER+SUHNER:

[82_MFBX-50-0-4/111_NE](#)