


Coaxial PCB Connector 82_MMCX-S50-0-2/111_K

Description

Straight PCB jack

Interface Standards
SUHNER-MMCX



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	6 GHz

Mechanical Data

Board mounting type	edge mount
Weight	0.0007 kg

Environmental Data

Operating temperature	-55 °C to 155 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	Gold Plating (Nickel underplated)
Body	Brass	Gold Plating (Nickel underplated)
Insulator	PFA / PTFE	

Related Documents

Outline drawing	DOU-00013081
Catalogue drawing	DCA-00013083

Ordering Information

Bulk 100 pcs package	82_MMCX-S50-0-2/111_KH
Tape and Reel package	82_MMCX-S50-0-2/111_KG
Single package	82_MMCX-S50-0-2/111_KE

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HUBER+SUHNER:

[82_MMCX-S50-0-2/111_KE](#)