


Adjustable Antenna 3D Pole and Wall Mount Bracket 9091.99.0267

Description

Down- / sidetilt and radial-turn bracket for SENCITY® Spot-S antennas
For outdoor and indoor applications

Two suitable hose clamps for pole mount option included



Technical Data

Mechanical Data

Dimensions (mm)	58 x 42 x 70 (Height x Width x Depth)
Mast diameter (mm)	25 - 85
Material	Stainless Steel

Max. tractive force 20N in x/y/z direction

Mounting material 2 screws M4 L=8mm and 2 hose clamps for pole-diameter 25 to 85 mm

Environmental Data

2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant
--	-----------

Related Documents

Mounting instruction	DOC-0000807712
Painting instruction	DOC-0000256180
Security instruction	DOC-0000278984
Outline drawing1	DOU-00353924

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HUBER+SUHNER:

9091.99.0267