


Flexible microwave cable EACON_6C Item: 84116403

Description

Eacon: Field mountable flexible microwave cables

50 Ohm, 18 GHz, 200°C, ø7.7 mm, FEP jacket



Technical Data

Construction

	Material	Detail	Diameter
Centre conductor	Copper, Silver plated	Wire	2.05 mm
Dielectric	PTFE-LD		6.2 mm
Outer conductor	Copper, Silver plated	wrapped Foil, 100%	6.42 mm
Outer conductor	Copper, Silver plated	Braid	7.1 mm
Jacket	FEP (Fluorinated ethylene propylene)	RAL 9010 - wh	7.7 mm +/- 0.1

Electrical Data

Impedance	50 Ω +/- 1
Operating Frequency	18 GHz
Capacitance	87 pF/m
Velocity of signal propagation	77 %
Signal delay	4.3 ns/m
Screening effectiveness	≥ 90 dB (up to 18 GHz)
Operating voltage	≤ 3.8 kV _{rms} (at sea level)

Mechanical Data

Weight	14.8 kg/100 m
Min. bending radius	static 24 mm
	dynamic 40 mm

Environmental Data

Temperature range	-55 °C ... +200 °C
Flame propagation test	MIL-T-87104 § 4.6.4.8, , FAR 25.869
Halogen free	No
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant
1907/2006/EC (REACH)	compliant
2000/53/EC (ELV)	compliant
2012/19/EU (WEEE)	no special marking needed

Additional Information

Remarks

(For details refer to the HUBER+SUHNER RF CABLES GENERAL CATALOGUE or contact your nearest HUBER+SUHNER partner)

Suitable Connectors

Cable group	U96 EACON_6C
-------------	--------------

Flexible microwave cable

EACON_6C Item: 84116403

Matrix typical Attenuation [formula: $(a \cdot f^{0.5} + b \cdot f)$] and maximum Power CW [formula: $(p/f^{0.5})$]

Coefficients:

a = 0.15

b = 0.0071

f_{max} = 18

P at 1GHz = 1582

Frequency	Nom. attenuation	Nom. attenuation	Max. CW power
(GHz)	(dB / m)	(dB / ft)	(W)
	sea level 25° C ambient temperature	sea level 25° C ambient temperature	sea level 40° C ambient temperature
0,9	0,15	0,045	1668
1,8	0,21	0,065	1179
2,7	0,27	0,081	963
3,6	0,31	0,095	834
4,5	0,35	0,107	746
5,4	0,39	0,118	681
6,3	0,42	0,128	630
7,2	0,45	0,138	590
8,1	0,48	0,148	556
9,0	0,51	0,157	527
9,9	0,54	0,165	503
10,8	0,57	0,174	481
11,7	0,6	0,182	463
12,6	0,62	0,190	446
13,5	0,65	0,197	431
14,4	0,67	0,205	417
15,3	0,7	0,212	404
16,2	0,72	0,219	393
17,1	0,74	0,226	383
18,0	0,76	0,233	373

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HUBER+SUHNER:](#)

[EACON_6C](#)