

Flexible RF cable

ENVIROFLEX_316_D-AM **Item: 85070084**

Description

Enviroflex: LSFH alternatives to RG cables

RG316D/RD316 LSFH, 50 Ohm, 6 GHz, 105°C, ø3.16 mm,
RADOX® jacket, Flame retardant, Bus qualified



Technical Data

Construction

	Material	Detail	Diameter
Centre conductor	Steel, Copper+Silver plated	Strand-07	0.54 mm
Dielectric	SPEX (Crosslink Foam PE)		1.53 mm
Outer conductor	Copper, Silver plated	Braid, 96%	1.99 mm
Outer conductor	Copper, Silver plated	Braid, 90 %	2.44 mm
Jacket	RADOX	black/bl line	3.16 mm +/- 0.08

Print: HUBER+SUHNER ENVIROFLEX 316 D-AM 50 Ohm (production order number)

Electrical Data

Impedance	50 Ω +/- 2
Operating Frequency	6 GHz
Capacitance	94.5 pF/m
Velocity of signal propagation	70.1 %
Signal delay	4.72 ns/m
Screening effectiveness	≥ 70 dB (up to 6 GHz)
Operating voltage	≤ 1.3 kV _{rms} (at sea level)
Test voltage	3 kV _{rms} (50 Hz/1 min)

Mechanical Data

Weight		2.1 kg/100 m
Min. bending radius	static	5 mm
	repeated (for ≤ 30000 bendings)	30 mm
	dynamic	30 mm

Environmental Data

Temperature range	-40 °C ... +105 °C
Installation temperature	-20 °C... +60 °C
Halogen test	IEC 60754
Halogen free	Yes
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant
1907/2006/EC (REACH)	compliant
2000/53/EC (ELV)	compliant
2012/19/EU (WEEE)	no special marking needed

Additional Information

ISO 6722-1 5.22 (UN ECE-R 118.01) compliant

Remarks

(For details refer to the HUBER+SUHNER RF CABLES GENERAL CATALOGUE or contact your nearest HUBER+SUHNER partner)

Suitable Connectors

Cable group	U4 2 mm / 50 Ohm
-------------	------------------

Flexible RF cable

ENVIROFLEX_316_D-AM Item: 85070084

Matrix typical Attenuation [formula: $(a \cdot f^{0.5} + b \cdot f)$] and maximum Power CW [formula: $(p/f^{0.5})$]

Coefficients:

a = 0.7648

b = 0.1301

 $f_{\max} = 6$

P at 1GHz = 110

Frequency	Nom. attenuation	Nom. attenuation	Max. CW power
(GHz)	(dB / m)	(dB / ft)	(W)
	sea level 25° C ambient temperature	sea level 25° C ambient temperature	sea level 40° C ambient temperature
0,3	0,46	0,140	201
0,6	0,67	0,204	142
0,9	0,84	0,257	116
1,2	0,99	0,303	100
1,5	1,13	0,345	90
1,8	1,26	0,384	82
2,1	1,38	0,421	76
2,4	1,5	0,456	71
2,7	1,61	0,490	67
3,0	1,71	0,523	64
3,3	1,82	0,554	61
3,6	1,92	0,585	58
3,9	2,02	0,615	56
4,2	2,11	0,644	54
4,5	2,21	0,673	52
4,8	2,3	0,701	50
5,1	2,39	0,729	49
5,4	2,48	0,756	47
5,7	2,57	0,783	46
6,0	2,65	0,809	45

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HUBER+SUHNER:](#)

[ENVIROFLEX_316_D-AM](#)