

## 3-Way Power Splitter K7431348

### Reactive Splitter

### Description

Installation Equipment for Sencity Special Communication Antennas:  
3-Way Power Splitter 380-512 MHz  
For indoor and outdoor use



### Technical Data

#### Electrical Data

Signal Band 1				
Frequency	0.38 - 0.512 GHz			
Insertion Loss	0.05 dB			
Max. Composite Power	1000 W			
Input 1				
Connector Type	7/16			
Connector Gender	jack (female)			
		Output 1	Output 2	Output 3
Connector Type	7/16	7/16	7/16	7/16
Connector Gender	jack (female)	jack (female)	jack (female)	jack (female)
Char. impedance	50 Ω			

VSWR < 1.1

#### Mechanical Data

Dimensions 409 x 82 x 82 mm (Height x Width x Length)

Packing size (mm): 425 x 93 x 107

#### Environmental Data

Environmental conditions indoor/outdoor  
2011/65/EU (RoHS - including compliant  
2015/863 and 2017/2102)  
WEEE 2002/96/EC no special marking needed

Material:

Case: Aluminum

Inner conductor: Brass

Mounting:

Bracket for wall mounting included in the scope of supply. For mounting to tubular masts use clamps as listed below (order separately).

#### Related Products

734364 Tension Band 120-140mm

#### Related Documents

Mounting instruction DOC-0000871752

## 3-Way Power Splitter K7431348

Security instruction  
Outline drawing

DOC-0000278984  
DOU-00397212

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HUBER+SUHNER:](#)

[K7431348](#)