

4-Way Power Splitter K7431358

Reactive Splitter

Description

Installation Equipment for Sencity Special Communication Antennas:
4-Way Splitter 380-512 MHz
For indoor and outdoor use



Technical Data

Electrical Data

| | Signal Band 1 | | | |
|----------------------|------------------|---------------|---------------|---------------|
| Frequency | 0.38 - 0.512 GHz | | | |
| Insertion Loss | 0.05 dB | | | |
| Max. Composite Power | 1000 W | | | |
| | Input 1 | | | |
| Connector Type | 7/16 | | | |
| Connector Gender | jack (female) | | | |
| | Output 1 | Output 2 | Output 3 | Output 4 |
| Connector Type | 7/16 | 7/16 | 7/16 | 7/16 |
| Connector Gender | jack (female) | jack (female) | jack (female) | jack (female) |
| Char. impedance | 50 Ω | | | |

VSWR > 1.1

Mechanical Data

Dimensions 409 x 82 x 82 mm (Height x Width x Length)

Packing size (mm): 425x93x107

Environmental Data

Environmental conditions indoor/outdoor
2011/65/EU (RoHS - including compliant
2015/863 and 2017/2102)
WEEE 2002/96/EC no special marking needed

Material:

Case: Aluminum

Inner conductor: Brass

Mounting:

Bracket for wall mounting included in the scope of supply. For mounting to tubular masts use clamps as listed below (order separately).

Related Products

734365 Tension Band 45-125mm

734364 Tension Band 120-140mm

4-Way Power Splitter K7431358

Related Documents

Mounting instruction
Security instruction
Outline drawing

DOC-0000871752
DOC-0000278984
DOU-00397214

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HUBER+SUHNER:](#)

[K7431358](#)