

PCDS_SCMS_SCMS_O320E_XX.X_MM

Description

Duplex patch cord, SC simplex to SC simplex, MM, duplex fig.8 2x2.0mm_XX.X_turquoise, OM3 BendOptimized



Features	Features
- Push-pull connector	
- One-piece design for easy and quick termination	
- High mechanical and thermal resistance according to Telcordia GR-326-CORE	

Technical Data

General Data

Description	Values
General Typ	Duplex SC patch cord
Operation temperature	-25 up to 70°C
Polarity	A-B / B-A straight polarity (standard)
UL Rating	UL 94 V-0
RoHS compliant 2001/65/EU	Yes
REACH compliant	Yes

Connector left

Description	Values
Connector typ	SC simplex
Polish	UPC
Color Housing	Aqua
Color Boot	Black / Red
Design connector acc. To	IEC 61754-4, TIA 604-3
Performance class H+S	M
Insertion loss 97% dB / mean dB	0.25 / 0.12
Return Loss	35
Durability	1000
Tensile load	2 x 100 N
Tensile load acc. To GR-326-COR	Fulfilled

Connector right


Description	Values
Connector typ	SC simplex
Polish	UPC
Color Housing	Aqua
Color Boot	Black / Red
Design connector acc. To	IEC 61754-4, TIA 604-3
Performance class H+S	M
Insertion loss 97% dB / mean dB	0.25 / 0.12
Return Loss	35
Durability	1000
Tensile load	2 x 100 N
Tensile load acc. To GR-326-COR	Fulfilled

PCDS_SCMS_SCMS_O320E_XX.X_MM

Cable

Description	Values
Cable typ	Duplex Cable Figure 8
Fiber count	2
Fiber	2 x 0.9 mm
Fiber type	G50/125-OM3 BendOptimized
Outer diameter	2 mm

Technical Drawing



Ordering information

Meter (m)	Item number	Description
1	85031194	PCDS_SCMS_SCMS_O320E_01.0_MM
2	85031195	PCDS_SCMS_SCMS_O320E_02.0_MM
3	85031196	PCDS_SCMS_SCMS_O320E_03.0_MM
5	85031197	PCDS_SCMS_SCMS_O320E_05.0_MM
6	85031198	PCDS_SCMS_SCMS_O320E_06.0_MM
7	85031199	PCDS_SCMS_SCMS_O320E_07.0_MM
10	85031200	PCDS_SCMS_SCMS_O320E_10.0_MM
15	85031201	PCDS_SCMS_SCMS_O320E_15.0_MM
20	85031202	PCDS_SCMS_SCMS_O320E_20.0_MM

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HUBER+SUHNER:

[PCDS_SCMS_SCMS_O320E_02.0_MM](#)