

RG_214_/U-60 Item: 22511566

RG: RG type RF cables

Construction

	Material	Detail	Diameter
Centre conductor	Copper, Silver plated	Strand-07	2.25 mm
Dielectric	PE (Polyethylene)		7.28 mm
Outer conductor	Copper, Tin plated	Braid, 93%	8 mm
Outer conductor	Copper, Tin plated	Braid, 95 %	8.7 mm
Jacket	PVC (Polyvinyl chloride)	RAL 9005 - bk	10.8 mm +/- 0.15

Electrical Data

Impedance		50 Ω +/- 2
Operating Frequency		6 GHz
Capacitance		101 pF/m
Velocity of signal propagation		66 %
Signal delay		5.03 ns/m
Screening effectiveness		≥ 71 dB (up to 1 GHz)
Operating voltage		≤ 5 kV _{rms} (at sea level)
Test voltage		10 kV _{rms} (50 Hz/1 min)
Voltage Rating UL		30 V
Phase vs Temperature	-40°C... + 70°C	
Phase vs Bending		9 °/GHz

Weight		18.9 kg/100 m
Min. bending radius	static	55 mm
		108 mm

Temperature range	-25 °C ... +85 °C
Temperature rating UL	60 °C
Installation temperature	-20 °C... +60 °C
Flame propagation test	UL (vertical flame test similar VW-1),
Halogen free	No
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant
1907/2006/EC (REACH)	compliant

MIL reference: M17/190-00001 (former reference: M17/75-RG214)

(For details refer to the HUBER+SUHNER RF CABLES GENERAL CATALOGUE or contact your nearest HUBER+SUHNER partner)

Cable group	U32 7 mm / 50 Ohm
-------------	-------------------

Flexible RF cable

RG_214_/U-60 Item: 22511566

Matrix typical Attenuation [formula: $(a \cdot f^{0.5} + b \cdot f)$] and maximum Power CW [formula: $(p/f^{0.5})$]

Coefficients:

a = 0.1884

b = 0.0646

f_{max} = 6

P at 1GHz = 324

Frequency	Nom. attenuation	Nom. attenuation	Max. CW power
(GHz)	(dB / m)	(dB / ft)	(W)
	sea level 25° C ambient temperature	sea level 25° C ambient temperature	sea level 40° C ambient temperature
0,3	0,12	0,037	592
0,6	0,18	0,056	418
0,9	0,24	0,072	342
1,2	0,28	0,087	296
1,5	0,33	0,100	265
1,8	0,37	0,112	241
2,1	0,41	0,125	224
2,4	0,45	0,136	209
2,7	0,48	0,148	197
3,0	0,52	0,159	187
3,3	0,56	0,169	178
3,6	0,59	0,180	171
3,9	0,62	0,190	164
4,2	0,66	0,200	158
4,5	0,69	0,210	153
4,8	0,72	0,220	148
5,1	0,75	0,230	143
5,4	0,79	0,240	139
5,7	0,82	0,249	136
6,0	0,85	0,259	132

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HUBER+SUHNER:

[RG_214_/U-60](#)