

Sencity Antenna 1356.19.0008

SPA-5600/40/14/0/V

Description

Linear polarised directional WiFi-Antenna
 IEEE 802.11 a/h
 Frequency-Band: 5.150GHz-5.875GHz
 WLAN
 Wall and mast mounting material included, supports mast diameter 40mm-60mm
 For indoor applications



Product Configuration

Technical Data

Electrical Data

	Band 1
Frequency (MHz)	5150 - 5875
VSWR	1.5
Impedance (Ohm)	50
Gain (dBi)	13.5
3dB beamwidth (h) (°)	40
3dB beamwidth (v) (°)	35
Front to back ratio (dB)	18
Vertical electrical tilt (°)	0

Ports

	Port 1
Connector	SMA, jack (female)
Polarization	vertical

General Data

DC Grounding	No
Composite Power max (W)	10

Mechanical Data

Dimensions (mm)	101 x 80 x 20 (Height x Width x Depth)
Weight (kg)	0.13
Mast diameter (mm)	40 - 60
Included mounting material	Wall and mast mounting bracket

Environmental Data

Environmental conditions	indoor
Operation temperature (°C)	-40 to 80
Storage temperature (°C)	-40 to 80
Transport temperature (°C)	-40 to 80
RoHS 2011/65/EC	compliant
REACH 2006/1907/EC	compliant

Material Data

Radome colour	RAL 7035 (light-grey)
Radome material	ASA (acrylic ester-styrene-acrylonitrile)
Back plate/base plate material	ASA (acrylic ester-styrene-acrylonitrile)

Sencity Antenna 1356.19.0008

Related Products

9091.99.0191 Wall Bracket

Related Documents

Mounting instruction	DOC-0000215556
Painting instruction	DOC-0000256180
Security instruction	DOC-0000278984
Outline drawing	DOU-00018660.1
3D-model	DOC-0000257636

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HUBER+SUHNER:](#)

[1356.19.0008](#)