

HUBER+SUHNER® DATA SHEET

RF TERMINATION: Type 65_MMCX-50-0-1

Rev.: G



Description

Standard Termination, Low Power

Product Configuration

Connector	MMCX plug (male)
Interface standard	HUBER+SUHNER-MMCX



Technical Data

Electrical Data

Nominal impedance	50 Ω
Frequency range	DC to 3 GHz
VSWR max.	1.22
Power rating	0.5 Watt average power up to 30 °C ambient temperature, linearly derated to 0 Watt at 85 °C ambient temperature.

Mechanical Data

Weight	0.0016 kg
--------	-----------

Environmental Data

Operating temperature	-55 °C to 85 °C
2002/95/EC (RoHS)	not compliant

Material Data

Piece Part

Centre contact	Copper Beryllium Alloy
Outer contact	Brass
Body	Brass
Insulator	PFA / PTFE

Surface Plating

Gold Plating (Nickel underplated)
Gold Plating (without Nickel underplating)
Gold Plating (without Nickel underplating)

Related Documents

Outline drawing	DOU-00008665
-----------------	--------------

Ordering Information

Single packaging	65_MMCX-50-0-1/111_OE
------------------	-----------------------

HUBER+SUHNER is certified according to ISO 9001 and ISO 14001

WAIVER!

It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical specifications and/or the fitness for any particular purpose. The facts and figures contained herein are carefully compiled to the best of our knowledge, but they are intended for general informational purposes only.



HUBER+SUHNER AG
RF Industrial
9100 Herisau, Switzerland
Phone +41 (0)71 353 41 11
Fax +41 (0)71 353 45 90
www.hubersuhner.com

HUBER+SUHNER – Excellence in Connectivity Solutions

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HUBER+SUHNER:

[65_MMCX-50-0-1/111_OE](#)