

# HUBER+SUHNER® DATA SHEET

## Coaxial Cable Connector: 11\_N-50-12-10/033\_-



### Description

Straight cable plug

QUICK-FIT connector

For outdoor applications

Water protection according to IP 68



### Technical Data

#### Electrical Data

Impedance	50 $\Omega$	
Interface frequency max.	11 GHz	
Frequency range	DC to 2.5 GHz	2.5 to 3 GHz
Return loss	$\geq 30$ dB	$\geq 28$ dB
Intermodulation	$\leq -155$ dBc (2 x 43 dBm carrier)	

#### Mechanical Data

Centre contact	plugged
Outer contact	clamped
Weight	0.1473 kg

#### Environmental Data

Operating Temperature	-40 °C to 85 °C
2002/95/EC (RoHS)	compliant

#### Material Data

Piece Parts	Material	Surface Plating
Centre contact	Bronze	Silver Plating
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	NR (Natural Rubber)	

### Related Documents

Outline drawing	DOU-00007284
Catalogue drawing	DOU-00007286
Assembly instruction	DOC-0000179113

### Ordering Information

Single package	11_N-50-12-10/033_-E
----------------	----------------------

### Additional Information

Suitable cables	SUCOFEED_1/2, SUCOFEED_1/2_FR, SUCOFEED_1/2_FR_UL, SUCOFEED_1/2_LW, Heliac LDF4-50A, NK Cables RF 1/2-50, Cellflex LCF12-50
Interface standards	IEC 61169-16_MIL-STD-348A/304_CEC 22210

HUBER+SUHNER is certified according to ISO 9001 and ISO 14001

#### WAIVER!

It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical contained specifications and/or the fitness for any particular purpose. The facts and figures herein are carefully compiled to the best of our knowledge, but they are intended for general informational purposes only.



**HUBER+SUHNER AG**  
RF Technology  
9100 Herisau, Switzerland  
Phone +41 (0)71 353 41 11  
Fax +41 (0)71 353 45 90  
www.hubersuhner.com

**HUBER+SUHNER – Excellence in Connectivity Solutions**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HUBER+SUHNER:

11\_N-50-12-10/033\_-E