

# HUBER+SUHNER® DATA SHEET

## Coaxial Cable Connector: 24\_BMA-50-3-5/119\_N

Rev.: D



### Description

Straight bulkhead cable feed through

Interface Standards

IEC 60169-33\_MIL-STD-348A/321



### Technical Data

#### Electrical Data

Impedance 50  $\Omega$   
Interface frequency max. 18 GHz

#### Mechanical Data

Centre contact soldered  
Outer contact crimped  
Weight 0.0039 kg

#### Environmental Data

Operating Temperature -65 °C to 125 °C  
2002/95/EC (RoHS) compliant

#### Material Data

##### Piece Parts

|                |                          |
|----------------|--------------------------|
| Centre contact | Copper Beryllium / Brass |
| Outer contact  | Copper Beryllium Alloy   |
| Body           | Stainless Steel          |
| Insulator      | PFA / PTFE               |
| Crimp ferrule  | Brass                    |

##### Surface Plating

Gold Plating (Nickel underplated)  
Gold Plating (without Nickel underplating)

SUCOPLATE (R) Plating

#### Related Documents

|                      |                |
|----------------------|----------------|
| Catalogue drawing    | DCA-00045260   |
| Assembly instruction | DOC-0000185322 |
| Mounting hole        | DOU-00008950   |

#### Ordering Information

Single package 24\_BMA-50-3-5/119\_NE

#### Additional Information

Suitable cables RG\_223\_U, ENVIROFLEX\_142, RG\_142\_B/U

HUBER+SUHNER is certified according to ISO 9001 and ISO 14001

#### WAIVER!

It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical contained specifications and/or the fitness for any particular purpose. The facts and figures herein are carefully compiled to the best of our knowledge, but they are intended for general informational purposes only.



**HUBER+SUHNER AG**

**RF Technology**

**9100 Herisau, Switzerland**

Phone +41 (0)71 353 41 11

Fax +41 (0)71 353 45 90

[www.hubersuhner.com](http://www.hubersuhner.com)

**HUBER+SUHNER – Excellence in Connectivity Solutions**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HUBER+SUHNER:

[24\\_BMA-50-3-5/119\\_NE](#)