

HUBER+SUHNER® DATA SHEET

Coaxial Cable Connector: 25_BMA-50-3-3/119_N



Description

Straight panel cable jack, flange mount

Interface Standards

IEC 60169-33_MIL-STD-348A/321



Technical Data

Electrical Data

Impedance 50 Ω
Interface frequency max. 18 GHz

Mechanical Data

Centre contact soldered
Outer contact crimped
Weight 0.0062 kg

Environmental Data

Operating Temperature -65 °C to 125 °C
2002/95/EC (RoHS) compliant

Material Data

Piece Parts

Centre contact	Copper Beryllium / Brass
Outer contact	Copper Beryllium Alloy
Body	Stainless Steel
Insulator	PFA / PTFE
Crimp ferrule	Brass

Surface Plating

Gold Plating (Nickel underplated)
Gold Plating (without Nickel underplating)

SUCOPLATE (R) Plating

Related Documents

Catalogue drawing	DCA-00009062
Assembly instruction	DOC-0000185322
Mounting hole	DOU-00008816

Ordering Information

Single package 25_BMA-50-3-3/119_NE

Additional Information

Suitable cables RG_223_U, ENVIROFLEX_142, RG_142_B/U

HUBER+SUHNER is certified according to ISO 9001 and ISO 14001

WAIVER!

It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical contained specifications and/or the fitness for any particular purpose. The facts and figures herein are carefully compiled to the best of our knowledge, but they are intended for general informational purposes only.



HUBER+SUHNER AG
RF Technology
9100 Herisau, Switzerland
Phone +41 (0)71 353 41 11
Fax +41 (0)71 353 45 90
www.hubersuhner.com

HUBER+SUHNER – Excellence in Connectivity Solutions

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HUBER+SUHNER:](#)

[25_BMA-50-3-3/119_NE](#)