


HIGH GRAPHICS PERFORMANCE WITH LOW POWER CONSUMPTION

conga-QAF




- Based on AMD Embedded G-Series Processors
- Best price/performance ratio
- High performance graphics



Formfactor	Qseven Form Factor, 70 x 70 mm
CPU	AMD Embedded G-Series Processors AMD G-T40E 1.0 GHz Dual Core L2 cache 512KB x2 6.4W TDP AMD G-T40R 1.0 GHz Single Core L2 cache 512KB 5.5W TDP AMD G-T16R 615 MHz Single Core L2 cache 512KB 4.5W TDP
DRAM	2 GByte DDR3L-1066 onboard memory, optional 4 GByte
Chipset	AMD A55E Controller Hub
Ethernet	Gigabit Ethernet and Intel® 82574
I/O Interfaces	4x PCI Express x1 lanes, 2x Serial ATA®, 8x USB 2.0, 1x SDIO to 8bit SD/MMC, 2x ExpressCard™, LPC Bus, I2C Bus
Mass Storage	Onboard SATA Solid State Drive up to 32 GByte (optional)
Sound	High Definition Audio Interface
Graphics	Integrated AMD Radeon™ HD 6250, DirectX®11 graphics with UVD 3.0, Dual Simultaneous Display Support
LVDS	18bit, 24bit, Dual 24bit, up to 1920x1200@60Hz;; Automatic Panel Detection via EDID/EPI
Digital Display	DisplayPort 1.1a or HDMI 1.3 port, resolutions up to 1920x1200@60Hz
congatec Board controller	Multi Stage Watchdog, non-volatile User Data Storage, Manufacturing and Board Information, Board Statistics, BIOS Setup Data, Backup, I2C bus (fast mode, 400 kHz, multi-master), Power Loss Controll
Embedded BIOS Features	AMI-Aptio 4MByte Flash BIOS with congatec Embedded BIOS features
Power Management	ACPI 3.0 with battery support
Operating Systems	Microsoft® Windows7, Microsoft® Windows XP, Microsoft® Windows® embedded Standard, Linux 2.6
Power Consumption	Typ. application: tbd., see manual for full details, CMOS Battery Backup
Temperature	Operating: 0 .. +60°C Storage: -20 .. +80°C
Humidity	Operating: 10 - 90% r. H. non cond. Storage: 5 - 95% r. H. non cond.
Size	70 x 70 mm (2.76" x 2.76")

conga-QAF | Block diagram



conga-QAF | Order Information

Article	PN	Description
conga-QAF/T40R-2G	015300	Qseven module with low power AMD G-Series Single Core 1.0GHz Processor T40R with 512kB L2 cache and 2GB DDR3 onboard memory.
conga-QAF/T40E-2G	015301	Qseven module with low power AMD G-Series dual core 1.0GHz processor T40E with 512kB L2 cache and 2GB DDR3 onboard memory.
conga-QAF/T40E-2G SSD4	015303	Qseven module with low power AMD G-Series dual core 1.0GHz processor T40E with 512kB L2 cache, 2GB DDR3 onboard memory and 4GB onboard MLC SATA Solid State Disk.
conga-QAF/T40R-2G SSD8	015304	Qseven module with low power AMD G-Series single core 1.0GHz processor T40R with 512kB L2 cache, 2GB DDR3 onboard memory and 8GB onboard MLC SATA Solid State Disk.
conga-QAF/T40E-4G	015306	Qseven module with low power AMD G-Series dual core 1.0GHz processor T40E with 512kB L2 cache and 4GB DDR3 onboard memory.
conga-QAF/T16R-1G	015307	Qseven module with low power AMD G-Series single core 615MHz processor T16R with 512kB L2 cache and 1GB DDR3 onboard memory.
QAF/HSP-B	015330	Standard heatspreader for Qseven module conga-QAF. All standoffs are with 2.7mm bore hole.
QAF/HSP-T	015331	Standard heatspreader for Qseven module conga-QAF. All standoffs are M2.5mm thread.
QAF/CSP-B 6mm	015332	Passive cooling solution with 6mm fin height for Qseven module conga-QAF. All standoffs are with 2.7mm bore hole.

Accessories		
conga-QEVAL	007003	Evaluation platform for Qseven 2.0 modules
conga-QKIT	077455	Starterkit for Qseven including conga-QEVAL, conga-LDVI/EPI, conga-FPA1, Dual DVI-D ADD2 Card, ATX power supply...
Qseven Mobility Kit	077460	Complete ready-to-use starter-kit for mobile applications
conga-MCB/Qseven DP	020731	Qseven mini carrier board for mobile applications with DisplayPort
conga-MCB/Qseven Cable Kit	14000041	Complete cable kit for Qseven mini carrier board
Qseven MXM connector Foxconn	400017	Socket for Qseven Carrier Boards. 10pcs package. Foxconn standard type, SMT, lead free, 230 positions, 0.50mm pitch, 7.8mm height.
Qseven MXM Connector Aces	400018	Socket for Qseven Carrier Boards. 10pcs package. ACES standard type, SMT, lead free, 230 positions, 0.50mm pitch, 7.8mm height.
conga-LDVI/EPI	011115	LVDS to DVI converter board for digital flat panels with onboard EEPROM

© 2017 congatec AG. All rights reserved.

All data is for information purposes only. Although all the information contained within this document is carefully checked, no guarantee of correctness is implied or expressed. Product names, logos, brands, and other trademarks featured or referred are the property of their respective trademark holders. These trademark holders are not affiliated with congatec AG. Rev. NOVEMBER 30, 2017 JK

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[congatec:](#)

[conga-QAF/T40E-2G SSD4](#)