

XpressGXA10-LP1150T

Low-profile PCIe Network Processing FPGA
Board Featuring 80G Ethernet

- Low-profile PCIe Altera Arria 10 GX 1150 KLE board
- Designed for ultra low latency applications
- PCIe Gen3 x8 interface
- 4 GB DDR4 (1x 72bits)
- Up to 72 MB QDR2+ (4x 18bits)
- Dual QSFP+ cages 10/40 GbE ports
- 16x transceiver expansion port



Target applications:

Finance
Acceleration
Data center
Networking
Security


now part of Intel

 **Arria[®]10**

 **PCI EXPRESS 3**

Contact :

Europe Sales Office
sales@reflexces.com

www.reflexces.com


North America Sales Office
salesusa@reflexces.com



XpressGXA10-LP1150T

Benefits

- On board one DDR4 plus four QDR2+ independent banks
- Fail safe configuration flash sector
- Configuration via protocol (CvP)
- JTAG connector
- High speed extension connector for inter board communication (16 transceiver lanes)



Full Specifications

FPGA and Configuration Modules

- ALTERA Arria 10 GX 20nm FPGA
- NOR Flash for Active Serial (AS) configuration mode (2 sector for fail safe feature)

Communication Interfaces

- PCI Express x8 (Gen 1, 2 or 3)
- 2x QSFP+ quad optical cage (2x 4 XCVR: 10.3125 Gb/s per link)
 - 10GbE/40GbE/80GbE networking interface
 - Other protocols supported by the QSFP modules

Memory

- On board 4GB DDR4
 - 1 bank 72 bits (ECC)
 - 2400MT/s (FPGA speed grade 1)
- On board QDR-II+ up to 72 Mb
 - 4 independent banks, 18-bits
 - 633MHz (FPGA speed grade 1)

Operating Range : 0°C to 40°C

Storage Temp Range : 0°C to 70°C

Power

- External auxiliary connector (12V)
- Max 80W
- The XpressGXA10-LP1150 is delivered with a custom passive heatsink

Deliverables

- Low-profile (half-height) form factor PCIe Board
- Board Support Package (Manual, Test Designs)
- PCIe Power Supply adapter cable (same as GPU)
- PCIe Low profile or Standard bracket
- JTAG adapter cable for external USB Blaster cable
- Mechanical files 3D DWF/STEP models and 2D drawings (upon request)
- SDK for Windows 10 64Bits
- SDK for Linux Debian Stretch 64Bits (on request for other Linux distribution)

Both SDK version are based on WinDriver driver

Ordering informations

Part number

- XpressGXA10-LP1150T

Description

- Altera Arria 10 GX 10AX115N2F40I1SG, 4GB DDR4, 4 banks of 72Mbit QDR2+ Xtrem

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ReFLEX CES:](#)

[XpressGXA10-LP1150T](#)